

DYMO
Labelling machine, Type: MOBILE

Order data

Order number	085500 MOBILE
GTIN	3501179782430
Item class	08P

Description
Version:

Robust portable labelling machines for fast and simple production of self-adhesive plastic labels. Permanent thermal transfer printing. Adjustable tape advance and reverse. Power supply from rechargeable **Li-ion battery**, mains charger. Simple text generation with quick-access buttons. **MobileLabeler with Bluetooth® connection**. Quick and problem-free setting up and **operation with smartphone or tablet**. **Intuitive operation and fee-free DYMO® Connect Mobile App** functions with iOS® or Android™ smartphones.

Generation of labels with frames, styles and popular Google® and Apple® fonts.

Use of Windows / Mac fonts. DYMO® Connect functions with spell-checker and Voice-to-Text.

Application:

The labels stick to nearly all smooth grease-free surfaces.

Supplied with:

Includes lettering tape black on white and user instructions. Including a Li-ion battery, USB charger cable, charging adapter, 1 × label cartridge 24 mm × 3 m black on white.

Note:

- **Different language versions can be installed.**
- **With German QWERTZ keyboard ex stock, French AZERTY keyboard available on a short lead time.**

Interface: Bluetooth interface

Type: D1

available tape widths: 6; 9; 12; 19; 24 mm
Special features: PC connection (Smartphone)
Length: 425 mm
Width: 225 mm
Height: 395 mm

Technical description

Type	D1
Tape cut-off type	automatic
Mains adaptor	including
Special features	PC connection (Smartphone)
available tape widths	6; 9; 12; 19; 24 mm
Length	425 mm
Interface	Bluetooth interface
Width	225 mm
Weight without battery	488 g
Type of rechargeable battery	Lithium-ion
Number of rechargeable batteries contained	1
Height	395 mm
Power supply	Mains operated
Type of product	Labelling machine