

Garant**Side lock arbor Form ADB with cooling channel bores, SK 30 short, Clamping
Ø D1: 6mm****Order data**

Order number	300048 6
GTIN	4045197944122
Item class	31A

Description**Version:****GARANT –**

All shanks hard turned (for smooth cutting action!). Balancing quality G 2.5 / G 25,000 rpm.
With Balluff/RFID chip bore.

With coolant supply holes that can be plugged.

Application:

For clamping tools with side flats to DIN 1835 B and DIN 6535 HB.

Optional extras:

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

Technical description

External Ø D	25 mm
Overhang dimension A	50 mm
Clamping Ø D ₁	6 mm
Spare clamping screw No. 30 9900	6
Adapter	SK 30 short
Standard	DIN 6359
Arbor standard	ISO 7388-1

Shape	ADB
Cooling channel bore	lockable
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HPC
Type of product	Side lock arbor

Accessories

Spare clamping screw for chucks with clamping \varnothing D1 6 mm	309900 6
---	----------