

Garant**Eco clamping toolholder SVJCL 93°, for indexable inserts VC., left-hand****Order data**

Order number	261305 20/16
GTIN	4045197945259
Item class	21U

Description**Version:**

GARANT eco system screw-on toolholder with internal coolant feed to the cutting edge. Cooling by means of precision nozzles effectively and efficiently reduces the thermal loading, since the coolant stream is optimally directed between the chip and cutting edge. This results in higher productivity, longer tool life and greater process reliability. With flank face cooling.

Note:

Coolant transfer only in conjunction with GARANT eco-system toolholders No. 317900 – 319886.

Technical description

Set of insert screws	269023 3
Shim screw	269013 1
Shim	259033 5
Insert size	16 mm
Functional width L ₄	25 mm
ISO code toolholder	SVJCR/L 2020X16

Shank size	20 mm
suitable indexable insert	VC.. 1604..
Head length L ₁	40 mm
Overall length L	99 mm
Series	Eco
Application type	left-hand
Through-coolant	yes
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/261305-20/16>