

Garant

Shrink-fit chuck with 4 cooling channel bores, nickel-plated, HSK-A 100 short, Clamping \varnothing D1: 8mm



Order data

Order number	308267 8
GTIN	4045197945389
Item class	31A

Description

Version:

- **High-temperature steel.**
- **Sizes 3 – 5 for carbide, from size 6 for HSS and carbide.**
- **With RFID/Balluffchip bore.**

Premium version: Nickel plated version with 4 pluggable **cooling channel bores**. Integral tool length adjustment (adjustment track 10 mm).

Application:

- **For holding end mills and drills with parallel shank to h6 tolerance.**
- **Suitable for inductive, contact and hot air shrink-fit units.**

Supplied with:

For chucks with length adjustment including a length adjustment screw (from clamping \varnothing D₁ 6 mm).

4 × M3 nozzle screws.

Optional extras:

Coolant tube No. 309880, socket wrench No. 309890, shrink-fit chuck extension No. 302410 – 302416, shrink-fit units No. 354210 – 354450, balancing screw set No. 309906 180.

Technical description

Overhang dimension A	85 mm
----------------------	-------

External \varnothing D	27 mm
\varnothing D ₂	21 mm
Cooling channel bore	lockable
Clamping \varnothing D ₁	8 mm
Adapter	HSK-A 100 short
Arbor standard	ISO 12164-1
Arbor standard	DIN 69893
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HSC
Machining strategy	HPC
Type of product	Shrink-fit chuck