

Garant
Side lock arbor Form ADB with cooling channel bores, nickel-plated, SK 40 short, Clamping \varnothing D1: 10mm

Order data

| | |
|--------------|---------------|
| Order number | 300120 10 |
| GTIN | 4045197945693 |
| Item class | 31A |

Description
Version:
GARANT –

All shanks hard turned (for smooth cutting action!). Balancing quality G 2.5 / G 25,000 rpm

With coolant supply holes that can be plugged.

Special nickel plating.

With Balluff/RFID chip bore.

Application:

For clamping tools with side flats to DIN 1835 B and DIN 6535 HB.

Optional extras:

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

Technical description

| | |
|---------------------------------------|-------------|
| Clamping \varnothing D ₁ | 10 mm |
| Spare clamping screw No. 30 9900 | 10 |
| External \varnothing D | 35 mm |
| Overhang dimension A | 50 mm |
| Adapter | SK 40 short |
| Standard | DIN 6359 |

| | |
|---------------------------------------|----------------------|
| Arbor standard | ISO 7388-1 |
| Shape | ADB |
| Cooling channel bore | lockable |
| Balance quality G at rotational speed | G 2.5 at 25,000 rpm |
| Concentricity | $\leq 3 \mu\text{m}$ |
| Machining strategy | HPC |
| Type of product | Side lock arbor |

Accessories

| | |
|--|-----------|
| Spare clamping screw for chucks with clamping \varnothing D1 10 mm | 309900 10 |
|--|-----------|