

Garant**Toolholder for metric profile broaching tools $\varnothing d = 16$ mm, Shank $\varnothing DS$: MK3mm****Order data**

| | |
|--------------|---------------|
| Order number | 293026 MK3 |
| GTIN | 4045197946119 |
| Item class | 29K |

Description**Suitable for:**

CNC and conventional machines.

Optional extras:

Positioning aid (No. 293000) and pin wrench (No. 293006).

Drive-out tang for MT shanks can be ordered under No. 293008 in the sizes MT2, MT3 and MT4.

Note:

- **Caution: Always use appropriate slotting tool \varnothing .**
- **Other shank connections on request.**

Technical description

| | |
|--------------------|-------|
| L | 76 mm |
| Shank length L_s | 86 mm |
| Shank type | MT3 |
| $\varnothing d$ | 16 mm |

| | |
|-----------------|---|
| Ø D | 58 mm |
| Arbor size | MT3 |
| Through-coolant | no |
| Type of product | Keyway broaching and profile slotting tool |