



Positive engagement double wedge clamp, Thread M: M12



Order data

Order number	370011 M12
GTIN	4046368801558
Item class	37M

Description

Version:

- Aluminium profile with steel wedge including screws.
- Extra-wide jaws, to allow the workpiece contour to be milled in.

Advantage:

- Positive engagement of workpieces, thus secure clamping.
- Clamping of 2 workpieces at the same time.

Note:

The locking plate is required for machining the double wedge clamp.

Technical description

Thread M	M12
Clamping force	15.58 kN
maximum tightening torque	38.4 Nm
B ₂	15.7 mm
H ₁	19.1 mm
B ₁	30.86 mm
Height H	38.1 mm

Length L	47.5 mm
Width B	76.2 mm
Type of product	Wedge clamp