

Garant
Solid carbide end mill HPC, DLC, Ø f8 DC: 10mm

Order data

Order number	202552 10
GTIN	4045197948274
Item class	11X

Description
Version:

Sturdy roughing end mill **without** knuckle profile.

With strong core, **special chip breaker recesses** and **large polished flutes**.

Application:

For roughing milling with high demands on the component surface.

Technical description

Shank $\varnothing D_s$	10 mm
Helix angle	45 degrees
Shank	DIN 6535 HA to h6
Feed f_z for side milling in short-chipping aluminium	0.11 mm
Shank form	HA
Corner chamfer width at 45°	0.2 mm
Tolerance nominal \varnothing	f8
Overall length L	80 mm
Recess $\varnothing D_1$	9.2 mm
No. of teeth Z	4
Direction of infeed	horizontal, oblique and vertical
Flute length L_c	30 mm
Feed f_z for slot milling in short-chipping aluminium	0.09 mm

Overhang length L_1 incl. recess	38 mm
Cutting edge $\varnothing D_c$	10 mm
Corner chamfer angle	45 degrees
Coating	DLC
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	W
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width a_e for milling operation	$0.3 \times D$ for side milling
Through-coolant	no
Machining strategy	HPC
Colour ring	yellow
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Aluminium	Suitable	480 m/min	N
Aluminium (short chipping)	suitable	440 m/min	N
Alu > 10% Si	suitable	400 m/min	N
PMMA acrylic	Suitable	200 m/min	N
PE-HD	Suitable	160 m/min	N
PA 66	Suitable	200 m/min	N
PEEK	Suitable	150 m/min	N
PF 31	Suitable	130 m/min	N
PVDF GF20	suitable	180 m/min	N
POM GF25	Suitable	160 m/min	N
PA 66 GF30	suitable	150 m/min	N

PEEK GF30	suitable	130 m/min	N
PTFE CF25	suitable	160 m/min	N
Hybrids	suitable only under restricted conditions	m/min	N
Honeycomb sandwich	suitable only under restricted conditions	300 m/min	N
Cu	Suitable	160 m/min	N
CuZn	Suitable	200 m/min	N
wet maximum	suitable		
wet minimum	suitable		
dry	suitable only under restricted conditions		
Air	Suitable		
Services			

Shank grinding Type HB

129100 HB