

**Garant**
**DNMG 150408, Type: HB7010-1**


### Order data

Order number	250868 HB7010-1
GTIN	4045197949172
Item class	21G

### Description

DNMG 150408 HB7010-1 Grade: HB7010-1  
 Chip breaker: SG  
 Cutting depth  $a_p$ : 1.5 - 6 mm  
 Feed  $f$ : 0.25 - 0.6 mm/rev.  
 Cutting speed  $v_c$  main application: 100 - 375 m/min

### Technical description

Main application	P
Finishing/roughing assignment	Roughing
Cutting speed $v_c$ main application	100 - 375 m/min
Cutting conditions	continuous
Feed $f$	0.25 - 0.6 mm/rev.
Grade	HB7010-1
Chip breaker	SG

Tool material	Carbide
Corner radius	0.8 mm
Cutting depth $a_p$	1.5 - 6 mm
Coating	coated
ISO code indexable insert	DNMG 150408
Number of changes/inserts	4
Type of product	Indexable insert for turning