

**Garant**
**DNMG 150412, Type: HB7020**


### Order data

Order number	250769 HB7020
GTIN	4045197949158
Item class	21G

### Description

DNMG 150412 HB7020 Grade: HB7020  
 Chip breaker: SM  
 Tolerance: M  
 Cutting depth  $a_p$ : 0.5 - 5 mm  
 Feed  $f$ : 0.2 - 0.5 mm/rev.  
 Cutting speed  $v_c$  main application: 120 - 350 m/min

### Technical description

Cutting conditions	slightly interrupted
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Main application	P
Cutting depth $a_p$	0.5 - 5 mm
Tool material	Carbide
Feed $f$	0.2 - 0.5 mm/rev.

Corner radius	1.2 mm
Grade	HB7020
Cutting speed $v_c$ main application	120 - 350 m/min
Chip breaker	SM
Coating	coated
ISO code indexable insert	DNMG 150412
Number of changes/inserts	4
Tolerance	M
Type of product	Indexable insert for turning