

Garant
DNMG 150412, Type: HB7020


Order data

Order number	250869 HB7020
GTIN	4045197949219
Item class	21G

Description

DNMG 150412 HB7020 Grade: HB7020
 Chip breaker: SG
 Cutting depth a_p : 1.5 - 6 mm
 Feed f : 0.25 - 0.6 mm/rev.
 Cutting speed v_c main application: 100 - 300 m/min

Technical description

Main application	P
Cutting speed v_c main application	100 - 300 m/min
Corner radius	1.2 mm
Tool material	Carbide
Cutting conditions	slightly interrupted
Chip breaker	SG
Cutting depth a_p	1.5 - 6 mm

Finishing/roughing assignment	Roughing
Grade	HB7020
Feed f	0.25 - 0.6 mm/rev.
Coating	coated
ISO code indexable insert	DNMG 150412
Number of changes/inserts	4
Type of product	Indexable insert for turning