

HALDER**Frame clamp, Type: 1****Order data**

Order number	370135 1
GTIN	4030618274193
Item class	37K

Description**Version:**

Clamping elements with replaceable jaws.

Advantage:

- **Angled arrangement of the movable jaws creates a pull-down effect.**
- **Solid construction of vibration-damping spheroidal graphite iron (GGG60).**
- **Optimum compatibility to the workpiece.**
- **Few interference contours.**
- **Clamping of large workpieces as big as the entire table.**
- **Lateral location bores for mounting longitudinal stops.**

Supplied with:

1 pc. interchangeable jaw (serrated / smooth).

Length: 185 mm

Width: 65 mm

Height: 135 mm

maximum tightening torque: 50 N·m

Clamping force: 20 kN

Technical description

Width	65 mm
Height	135 mm
maximum tightening torque	50 N·m
Clamping force	20 kN
Length	185 mm
Type of product	Wedge clamp