



Softcut® 45° high-performance indexable face mill, with bore, Ø D / number of effective cutting edges Z: 125/10_ mm

Order data

Order number	213555 125/10_
GTIN	4045197953049
Item class	210

Description

Version:

High number of cutting edges for very high productivity. Positive rake for soft cut and low power consumption. Individual tool geometry ensures very smooth cutting.

Note:

Use GARANT torque screwdriver TQ No. **211750 3.0** with bit No. **674252 15IP**.

Setting angle κ : 45 degrees

Spacing of the milling cutter's cutting edges: unequal spacing

Through-coolant: ja

Machining strategy: MTC

Tool exchange: PowerCard

Technical description

Setting angle κ	degrees
Machining strategy	MTC
Shank type	with bore
Milling application	
Setting angle κ	degrees
Milling head suitable for insert shape	
Spacing of the cutters	unequal spacing
Through-coolant	yes
Setting angle κ	45 degrees
Tool exchange	PowerCard

Norm

Type of product