

HOLEX
Face mill arbor with cooling channel bore, HSK-A 100 A = 100, Spigot Ø d1: 40mm

Order data

| | |
|--------------|---------------|
| Order number | 306687 40 |
| GTIN | 4045197954374 |
| Item class | 32A |

Description
Version:

- **Clamping Ø 40 with 4 tapped holes for drive blocks to DIN 2079.**
- **With Balluff/RFID chip bore.**
- **Increased collar contact surface.**
- **HSK mating faces machined.**

With **cooling channel bores.**

Application:

For clamping shell end mills and milling cutter heads.

Supplied with:

Lock screw.

Optional extras:

Coolant tube No. 309880, socket wrench for coolant tubes No. 309890, toggle spanner No. 309840.

Technical description

| | |
|---|--------|
| Suitable toggle spanner No. 309840 | 40 |
| Milling mandrel length L ₄ | 27 mm |
| Spare milling cutter lock screw No. 309860 / 309861 | 40 |
| Overhang dimension A | 100 mm |

| | |
|---------------------------------------|---------------------|
| External Ø D | 89 mm |
| Clamping Ø D ₁ | 40 mm |
| Adapter | HSK-A 100 A = 100 |
| Arbor standard | ISO 12164-1 |
| Arbor standard | DIN 69882-3 |
| Arbor standard | DIN 69893 |
| Shape | A |
| Cooling channel bore | not pluggable |
| Balance quality G at rotational speed | G 2.5 at 25,000 rpm |
| Concentricity | ≤ 6 µm |
| Machining strategy | HPC |
| Type of product | Milling head arbor |