


Jobber drill HSS N, TiN, Ø DC h8: 3,9mm

Order data

Order number	114360 3,9
GTIN	4045197016454
Item class	12B

Description
Version:

Standard core without core taper.
Precision ground point.

Profile ground:

High concentricity and pitch accuracy, drills for series production use.
With point geometry shape C from size 2.4 mm

Recommendation:
Maximum drilling depth:

$$L_2 = L_c - 1.5 \times D_c$$

Technical description

Nominal Ø D _c	3.9 mm
Feed f in steel < 500 N/mm ²	0.05 mm/rev.
Number of cutting edges Z	2
Flute length L _c	43 mm
Tolerance nominal Ø	h8
Shank Ø D _s	3.9 mm
Overall length L	75 mm
Standard	DIN 338
recommended maximum drilling depth L ₂	37.2 mm
Point angle	118 degrees

Shank	Plain shank
Coating	TiN
Tool material	HSS
Type	N
Helix angle	35-40 degrees
Through-coolant	no
Colour ring	without
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	56 m/min	N
Alu > 10% Si	suitable only under restricted conditions	50 m/min	N
Steel < 500 N/mm ²	suitable	50 m/min	P
Steel < 750 N/mm ²	suitable	37 m/min	P
Steel < 900 N/mm ²	suitable	31 m/min	P
Steel < 1100 N/mm ²	suitable only under restricted conditions	12 m/min	P
Steel < 1400 N/mm ²	suitable only under restricted conditions	10 m/min	P
INOX < 900 N/mm ²	suitable only under restricted conditions	15 m/min	M
INOX > 900 N/mm ²	suitable only under restricted conditions	10 m/min	M
Ti > 850 N/mm ²	suitable only under restricted conditions	6 m/min	S
GG(G)	suitable	31 m/min	K
CuZn	suitable only under restricted conditions	80 m/min	N

Oil	suitable
wet maximum	suitable