




Permanent magnetic chuck, with parallel pole distribution, Chuck Ø: 160mm



Order data

Order number	380777 160
GTIN	2050001943699
Item class	33S

Description

Version:

Powerful magnetic system with **neodymium** magnets and low magnetic field height.

Continuously adjustable magnetic force.

Application:

For grinding and turning.

For clamping small and thin to large workpieces.

Note:

The centre can be bored out to size "J".

Technical description

Grinding allowance in pole area	6 mm
Centre Ø	125 mm
Centring hole depth	4 mm
Magnetic field height	10 mm
Pitch circle Ø	142 mm

Parallel pole distribution	8+3 mm
Height tolerance	0 / -1 mm
Nominal clamping force	100 N/cm ²
Height	57 mm
Weight	8 kg
Thread Ø	4×M8
possible to bore out to centre hole "J"	15×6 mm
Chuck Ø	160 mm
Type of product	Magnetic clamping chuck