

**Permanent magnetic chuck, with parallel pole distribution, Chuck Ø: 200mm****Order data**

Order number	380777 200
GTIN	2050001944405
Item class	33S

Description**Version:**

Powerful magnetic system with **neodymium** magnets and low magnetic field height.

Continuously adjustable magnetic force.

Application:

For grinding and turning.

For clamping small and thin to large workpieces.

Note:

The centre can be bored out to size "J".

Technical description

Centre Ø	150 mm
Weight	13 kg
Centring hole depth	4 mm
Height	57 mm
Thread Ø	4×M8

Nominal clamping force	100 N/cm ²
possible to bore out to centre hole "J"	20×6 mm
Height tolerance	0 / -1 mm
Pitch circle Ø	180 mm
Magnetic field height	10 mm
Chuck Ø	200 mm
Parallel pole distribution	8+3 mm
Grinding allowance in pole area	6 mm
Type of product	Magnetic clamping chuck