



Permanent magnetic chuck, with parallel pole distribution, Chuck Ø: 250mm



Order data

Order number	380777 250
GTIN	2050001944412
Item class	33S

Description

Version:

Powerful magnetic system with **neodymium** magnets and low magnetic field height.

Continuously adjustable magnetic force.

Application:

For grinding and turning.

For clamping small and thin to large workpieces.

Note:

The centre can be bored out to size "J".

Technical description

Grinding allowance in pole area	6 mm
Height tolerance	0 / -1 mm
possible to bore out to centre hole "J"	25×20 mm
Weight	20 kg
Centre Ø	200 mm

Thread Ø	4×M8
Chuck Ø	250 mm
Centring hole depth	4 mm
Magnetic field height	10 mm
Pitch circle Ø	232 mm
Nominal clamping force	150 N/cm ²
Height	57 mm
Parallel pole distribution	12+3 mm
Type of product	Magnetic clamping chuck