



Permanent magnetic chuck, with parallel pole distribution, Chuck Ø: 300mm



Order data

Order number	380777 300
GTIN	2050001944429
Item class	33S

Description

Version:

Powerful magnetic system with **neodymium** magnets and low magnetic field height.

Continuously adjustable magnetic force.

Application:

For grinding and turning.

For clamping small and thin to large workpieces.

Note:

The centre can be bored out to size "J".

Technical description

possible to bore out to centre hole "J"	25×20 mm
Height tolerance	0 / -1 mm
Grinding allowance in pole area	6 mm
Magnetic field height	10 mm
Height	62 mm

Centre Ø	250 mm
Nominal clamping force	150 N/cm ²
Thread Ø	4×M8
Centring hole depth	4 mm
Parallel pole distribution	12+3 mm
Pitch circle Ø	285 mm
Chuck Ø	300 mm
Weight	31 kg
Type of product	Magnetic clamping chuck