

**Permanent magnetic chuck, with parallel pole distribution, Chuck Ø: 200mm****Order data**

Order number	380776 200
GTIN	2050001943651
Item class	33S

Description**Version:**

Powerful magnetic system with **neodymium** magnets and low magnetic field height.

Continuously adjustable magnetic force.

Application:

For grinding and turning.

For clamping small and thin to medium workpieces.

Note:

The centre can be bored out to size "J".

Technical description

possible to bore out to centre hole "J"	200×5 mm
Pitch circle Ø	154 mm
Weight	15 kg
Nominal clamping force	100 N/cm ²
Grinding allowance in pole area	5 mm

Centre Ø	150 mm
Chuck Ø	200 mm
Parallel pole distribution	1.9 mm
Height	57 mm
Thread Ø	4×M8
Magnetic field height	8 mm
Centring hole depth	4 mm
Height tolerance	0 / -1 mm
Type of product	Magnetic clamping chuck