



## HSS jobber drill N, uncoated, Ø DC h8: 51mm



### Order data

Order number	116320 51
GTIN	4045197955708
Item class	12C

### Description

#### Version:

Special surface treatment, resulting in reduced tendency to edge build-up **and improved chip evacuation.**

#### Recommendation:

#### Maximum drilling depth:

$$L_2 = L_c - 1.5 \times D_c.$$

#### Note:

For suitable reducing adapters for tools with MT shanks see **No. 343000-343530.**

### Technical description

Flute length $L_c$	225 mm
Overall length $L$	412 mm
Morse taper MT size	5
recommended maximum drilling depth $L_2$	148.5 mm
Tolerance nominal $\varnothing$	h8
Nominal $\varnothing D_c$	51 mm
Standard	DIN 345
Number of cutting edges $Z$	2
Feed $f$ in steel $< 750 \text{ N/mm}^2$	0.32 mm/rev.
Point angle	118 degrees
Shank	Morse taper

Coating	uncoated
Tool material	HSS
Type	N
Helix angle	20-30 degrees
Through-coolant	no
Colour ring	without
Type of product	Jobber drill

### User data

	Suitability	V <sub>c</sub>	ISO code
Steel < 500 N/mm <sup>2</sup>	suitable	40 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	30 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable only under restricted conditions	25 m/min	P
GG(G)	suitable only under restricted conditions	25 m/min	K
Oil	suitable		
wet maximum	suitable		