

Garant**Pair of wheeled subframes for a mobile drawer cabinet Direction of pushing from the front of the drawer, Type: R36E****Order data**

| | |
|--------------|---------------|
| Order number | 942947 R36E |
| GTIN | 4045197526366 |
| Item class | 91H |

Description**Version:**

Pair of wheeled subframes - each consisting of 2 ball-bearing mounted wheels linked by a transverse subframe; one subframe with fixed wheels, the other with castors; wheel Ø 100 mm, with parking brake. **Note the movement direction of the wheels.** Load capacity 600 kg evenly distributed.

Suitable for:

Pair of wheeled subframes to fit tool cabinet shells of product group 94 (up to 08/2019) with **dimensions 27×36 units, 36×36 units**. For reasons of safety (risk of tipping over), the maximum usable height of the cabinet body is 900 mm (for 27×36 units) or 1225 mm (36×36 units). **Push the cabinet from the front of the drawers.**

Note:

- **Drawers in mobile tool cabinets must be fitted with individual drawer locking. This locks the drawer automatically on closing, so that it cannot open during transport. Individual drawer locking for drawers in product group 94 (up to 08/2019) can be found under No. 949605 in the spare parts list.**
- **When checking that the load capacity of the wheels (600 kg) is not exceeded, please make allowance for the tare weight of the cabinet itself.**
- **Please note the desired direction of movement of the wheels.**

Technical description

| | |
|--|-------------------------|
| total maximum load capacity | 600 kg |
| Castor Ø | 100 mm |
| Number of castors with parking brake | 2 |
| Direction of running | Direction cabinet width |
| Type | R36E |
| Fixed wheel Ø | 100 mm |
| Number of fixed wheels without parking brake | 2 |
| Type of product | Roller |