



## HOLEX CleverDrill jobber drill, long, HSS N, uncoated, Ø DC h8: 7,2 mm



### Order data

Order number	116050 7,2
GTIN	4045197956439
Item class	12B

### Description

#### Version:

**HOLEX CleverDrill** – Sturdy drill for all standard applications. Improved spot drilling behaviour due to cross-ground form. Standard core thickness and core taper. Profile ground. Surface: Bronze-coloured tempered helical flutes.

#### Recommendation:

#### Maximum drilling depth:

$$L_2 = L_c - 1.5 \times D_c$$

#### Note:

Suitable NC spotting drills No. 112120, 112140 and 112170 with **142° tip angle** for enhanced process reliability

Through-coolant: no

Standard: DIN 340

Tolerance nominal Ø: h8

Point angle: 130 degrees

Number of cutting edges Z: 2

recommended maximum drilling depth  $L_2$ : 91.2 mm

Flute length  $L_c$ : 102 mm

Overall length L: 156 mm

Shank Ø  $D_s$ : 7.2 mm

### Technical description

Nominal Ø $D_c$	7.2 mm
Flute length $L_c$	102 mm
recommended maximum drilling depth $L_2$	91.2 mm
Standard	DIN 340

Number of cutting edges Z	2
Overall length L	156 mm
Tolerance nominal Ø	h8
Shank Ø D <sub>s</sub>	7.2 mm
Point angle	130 degrees
Series	HOLEX CleverDrill
Coating	uncoated
Tool material	HSS
Type	N
Shank	Plain shank
Through-coolant	no
Colour ring	without
Type of product	Jobber drill