



HOLEX CleverDrill jobber drill, long, HSS N, uncoated, Ø DC h8: 7,5 mm



Order data

Order number	116050 7,5
GTIN	4045197956446
Item class	12B

Description

Version:

HOLEX CleverDrill – Sturdy drill for all standard applications. Improved spot drilling behaviour due to cross-ground form. Standard core thickness and core taper. Profile ground. Surface: Bronze-coloured tempered helical flutes.

Recommendation:

Maximum drilling depth:
flute length (see table) less 1.5×nominal Ø.

Note:

Suitable NC spotting drills No. 112120, 112140 and 112170 with **142° tip angle** for enhanced process reliability

Through-coolant: no

Standard: DIN 340

Tolerance nominal Ø: h8

Point angle: 130 degrees

Number of cutting edges Z: 2

recommended maximum drilling depth L₂: 90.75 mm

Flute length L_c: 102 mm

Overall length L: 156 mm

Shank Ø D_s: 7.5 mm

Technical description

Tolerance nominal Ø	h8
Standard	DIN 340
Flute length L _c	102 mm
Number of cutting edges Z	2

recommended maximum drilling depth L_2	90.75 mm
Nominal $\varnothing D_c$	7.5 mm
Shank $\varnothing D_s$	7.5 mm
Overall length L	156 mm
Point angle	130 degrees
Series	HOLEX CleverDrill
Coating	uncoated
Tool material	HSS
Type	N
Shank	Plain shank
Through-coolant	no
Colour ring	without
Type of product	Jobber drill