



## Self-levelling cross-hair laser LINO, Type: L2G



### Order data

Order number	468481 L2G
GTIN	7640110697535
Item class	47C

### Description

#### Version:

Robust, ergonomic plastic casing; proof against dust and splashed water. **With green laser lines for optimum visibility. Up to 400% better visibility than red laser lines.**

Pulse function with power-saving mode. **Very long working life** of up to 44 h due to Li-ion battery. The magnetic adapter can be attached to any wall that has steel elements. **The magnet can be freely pivoted and easily released.** Locking for inclined projections and for protection in transport.

#### Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

#### Supplied with:

Supplied with adapter, Li-ion battery, charger, battery holder, target board and case.

### Technical description

Levelling range	±4 degrees
Width	60 mm

IP Index of Protection	IP 54
Error limit	0.2 mm/m
Threaded socket for stand	1/4 UNC in
Range	35 m
Depth	100 mm
Laser class	2
Range with receiver	80 m
Weight	530 g
Height	110 mm
Colour of the laser	green
Number of rechargeable batteries contained	1
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Type of product	Cross laser

---

## Accessories

Alkaline-manganese batteries International size LR6	081561 LR6
-----------------------------------------------------	------------