

## Garant

### GARANT Master TM plain shank thread mill with countersink 2×D, TiAlN, G: G1/16



#### Order data

Order number	139715 G1/16
GTIN	4045197956934
Item class	11D

#### Description

##### Version:

Solid carbide thread milling cutters **with irregular cutting edge spacing and an increased number of cutting edges**. Due to the **irregular cutting edge spacing** they achieve very **smooth running** and **long tool life**.

**Newly developed universal geometry** and **high-performance coating** for use across a wide spectrum of materials.

- **Significantly reduced vibration due to irregular cutting edge spacing.**
- **Increased number of cutting edges.**
- **New coating for optimum wear resistance.**
- **Corrected thread profile for avoidance of profile distortions.**

##### Advantage:

Incorporating a countersink profile for a 90° countersink and thread milling in a single operation.

##### Application:

For **Whitworth parallel pipe threads** DIN-ISO 228/1 (threads that do not form a seal within the connections). **Suitable for internal and external threads.**

##### Note:

HB and HE shanks are available at the same price as HA.

Order **HB** shank: with **No. 139715 + 129100 HB**.

Order **HE** shank: with **No. 139715 + 129100 HE**.

#### Technical description

No. of teeth Z	4
Thread size	G1/16

Number of clamping slots	4
Shank length $L_s$	40 mm
Feed $f_z$ in steel < 750 N/mm <sup>2</sup>	0.06 mm
Threads per inch	28
Thread pitch	0.91 mm
Overall length L	75 mm
Flute length $L_c$	15.87 mm
Thread depth	15.87 mm
Shank $\varnothing D_s$	10 mm
Series	Master TM
Nominal $\varnothing D_c$	6.2 mm
Application for type of drilling	up to 2×D for blind holes
Application for type of drilling	up to 2×D for through holes
Programming value for countersink $L_1$	16.88 mm
Neck $\varnothing D_1$	8.3 mm
For use with external threads	up to 2×D for bolt threads
Coating	TiAlN
Thread type	G
Thread type	G-LH
Flank angle	55 degrees
Tool material	Solid carbide
Shank	DIN 6535 HA to h6
Through-coolant	yes
Spacing of the cutters	unequal spacing
Countersink angle	90 degrees
Colour ring	green
Internal/external application	Internal
Type of product	thread milling cutter

## User data

	Suitability	$V_c$	ISO code
Alu plastics	suitable	220 m/min	N
Aluminium (short chipping)	suitable	220 m/min	N
Alu > 10% Si	suitable	180 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	140 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	130 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	120 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	90 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	80 m/min	P
Steel < 50 HRC	suitable only under restricted conditions	45 m/min	H
TOOLOX 33	suitable	85 m/min	H
TOOLOX 44	suitable	50 m/min	H
INOX < 900 N/mm <sup>2</sup>	suitable	82 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	75 m/min	M
Ti > 850 N/mm <sup>2</sup>	suitable	50 m/min	S
GG(G)	suitable	120 m/min	K
CuZn	suitable	200 m/min	N
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable		
Air	suitable		

## Services

Shank grinding Type HE	129100 HE
Shank grinding Type HB	129100 HB