



## Cordless impact wrench, Type: M18FMTF12



### Order data

Order number	074010 M18FMTF12
GTIN	4002395289202
Item class	03L

### Description

#### Version:

Robust and **powerful FUEL™ cordless impact wrench** with **brushless POWERSTATE™ EC motor** for long motor service life and high energy efficiency. Sturdy **metal gearbox casing** and ergonomic **central handle with soft-grip coating**. Stage of charge display, LED illumination of the working area. Reversible, with electronic speed control. **REDLINK PLUS™ electronics** – for unique power management:

- **With system communication between the drive machine and battery.**
- **With overload protection for longer working life of the battery, motor, and gearbox.**

DRIVE CONTROL™ permits quick switching between the 4 available settings with different speeds and torques. M18 FUEL™ Impact wrench with **610 Nm** torque, yet only 172 mm long. Sturdy metal gearbox casing.

#### Standard:

Robust and **powerful FUEL™ cordless impact screwdriver** with **brushless POWERSTATE™ EC motor** for long motor service life and high energy efficiency.

#### Supplied with:

Supplied with 2× Li-ion batteries, charger, HD box, belt clip.

#### Note:

For matching spare batteries and accessories see from No. 073808.

Packaging: Modular case (HD=Heavy Duty)

suitable battery - supplier / battery type / voltage: Milwaukee type B 18 V

Manufacturer's designation: M18FMTIWF12-502X

Number of rechargeable batteries contained: 2

Type of rechargeable battery: Lithium-ion

Battery capacity: 5 Ah

Battery voltage: 18 V

maximum torque 1st step: 130 Nm

## Technical description

maximum torque 2nd step	550 Nm
Packaging	Modular case (HD=Heavy Duty)
maximum torque 1st step	130 Nm
Number of impacts 2nd stage	2700 rpm
Tool arbor size	1/2 inch
maximum torque 3rd step	610 Nm
Weight	2.4 kg
Manufacturer's designation	M18FMTIWF12-502X
maximum screw $\varnothing$ (8.8 - 12.9)	M20
Battery capacity	5 Ah
Number of impacts 3rd stage	3000 rpm
typical application	Heavy Duty
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
Tool arbor drive profile	External square drive
Battery voltage	18 V
Number of impacts 1st stage	420 rpm
Number of rechargeable batteries contained	2
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Type of product	Impact wrench

## Accessories

Battery charger Type M1218C	073840 M1218C
Li-ion system M18B5 Rechargeable battery type, battery voltage MB18 V	073816 MB18
Battery charger Type M1218FC	073840 M1218FC