

Edge finder TN, Contact point Ø: 10mm



Order data

Order number	359005 10
GTIN	4260192272944
Item class	38D

Description

Version:

The contact point has a flexible connection to the body via a spring, with an **alignment accuracy of 0.01 mm.**

All parts fully hardened and ground.

Non-magnetic.

Application:

For alignment of component reference surfaces or edges.

Spindle speed approx. 600 rpm.

Technical description

Overall length	84 mm
Contact point Ø	10 mm
Tool shank Ø	10 mm
Type of product	Probes

