

## Garant

### End mill HSS-PM, TiAlN, Ø k10 DC: 14mm



## Order data

Order number	191581 14
GTIN	4045197973795
Item class	11W

## Description

### Version:

Multi-flute end mill, for highest metal removal rate demands. Centre cutting edge geometry for plunging. **Eccentric relief ground**. For peripheral milling as a finishing operation, **producing very high surface finish quality**.

### Advantage:

**Excellent results** when **milling dry**.

## Technical description

Shank	DIN 1835 B to h6
Helix angle	50 degrees
Direction of infeed	horizontal, oblique and vertical
Tolerance nominal Ø	k10
Shank Ø D <sub>s</sub>	12 mm
Corner chamfer width at 45°	0.25 mm
Overall length L	83 mm
Flute length L <sub>c</sub>	26 mm
No. of teeth Z	4
Feed f <sub>z</sub> for slot milling in steel < 750 N/mm <sup>2</sup>	0.058 mm
Cutting edge Ø D <sub>c</sub>	14 mm
Corner chamfer angle	45 degrees

Coating	TiAlN
Tool material	HSS PM
Standard	DIN 844 B
Type	N
Through-coolant	no
Colour ring	without
Type of product	End / face mill

### User data

	Suitability	V <sub>c</sub>	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	138 m/min	N
Alu > 10% Si	suitable only under restricted conditions	110 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	83 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	64 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	64 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	37 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable only under restricted conditions	32 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	23 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable only under restricted conditions	18 m/min	M
GG(G)	suitable only under restricted conditions	55 m/min	K
CuZn	suitable only under restricted conditions	110 m/min	N
Uni	suitable		
wet maximum	suitable		
dry	suitable		
Air	suitable		

