



## External micrometer with disc anvils $\varnothing$ 25 mm, Measuring range: 25-50mm



### Order data

Order number	422990 25-50
GTIN	4250099616361
Item class	46P

### Description

#### Version:

Disc anvil of hardened steel in flat version, **without recess**. Hardened and ground measuring spindle. Higher accuracy than **DIN 863**. Locking by clamping device. With ratchet and hand temperature protection. Clearly engraved black divisions and numerals.

#### Application:

For determining the tooth widths of spur and helical gears from module 0.6.

### Technical description

Type of reading parts	engraved, black
Type of spindle	hardened and ground
Calibration	B1
Locking	by clamping device
Barrel $\varnothing$	24 mm
Scale divisions	0.01 mm
Spindle $\varnothing$	8 mm
Micrometer barrel graduations	1/100 mm
Measuring range	25 - 50 mm
Type of operating parts	Hand temperature protection

Error limit	4 µm
Standard	Manufacturer's standard
Ratchet	yes
Disc anvil	yes
Measurement technology	analogue
Packaging	sturdy box
Type of product	External micrometer

### Services

Calibration External micrometer without setting dimension maximum measuring range 100 mm	022000 100
DAkkS calibration External micrometer without setting dimension maximum measuring range 100 mm	022010 100

### Accessories

Micrometer setting standard overall length 25 mm	421100 25
--	-----------