



External micrometer with disc anvils \varnothing 25 mm, Measuring range: 0-25mm



Order data

Order number	422990 0-25
GTIN	4250099616354
Item class	46P

Description

Version:

Disc anvil of hardened steel in flat version, **without recess**. Hardened and ground measuring spindle. Higher accuracy than **DIN 863**. Locking by clamping device. With ratchet and hand temperature protection. Clearly engraved black divisions and numerals.

Application:

For determining the tooth widths of spur and helical gears from module 0.6.

Technical description

Micrometer barrel graduations	1/100 mm
Calibration	B1
Type of spindle	hardened and ground
Spindle \varnothing	8 mm
Scale divisions	0.01 mm
Barrel \varnothing	24 mm
Measuring range	0 - 25 mm
Type of reading parts	engraved, black
Locking	by clamping device
Type of operating parts	Hand temperature protection

Error limit	4 µm
Standard	Manufacturer's standard
Ratchet	yes
Disc anvil	yes
Measurement technology	analogue
Packaging	sturdy box
Type of product	External micrometer

Services

DAkkS calibration External micrometer without setting dimension maximum measuring range 100 mm	022010 100
Calibration External micrometer without setting dimension maximum measuring range 25 mm	022000 25