


**VHB™ Power adhesive tape, Manufacturer's designation: GPH**

---

**Order data**

Order number	083784 GPH
GTIN	4054596233782
Item class	08M

---

**Description****Version:**

**Double-sided** high-performance **adhesive tape** of pure acrylate adhesive (VHB) for permanent strong bonds. High instant tack, high resistance to temperature, weather, UV and solvents. Excellent sealing function, vibration-damping.

GPH#110GF for metals, high temperatures and prior to powder-coating. **19 mm × 3 m.**

**Application:**

Suitable for metals, painted surfaces, painted wood, glass, ceramics and many plastics. For use indoors and outdoors.

Length: 3 m

Width: 19 mm

Colour: grey

Short-term temperature-resistant to: 230 °C

Long-term temperature-resistant to: 150 °C

---

**Technical description**

Manufacturer's designation	GPH-110GF
Thickness	1.1 mm

Width	19 mm
Colour	grey
Length	3 m
Material of covering	Siliconised PE film
Number of adhesive tapes	1
Storage humidity	40 - 65 %
Storage temperature	16 - 25 °C
Adhesive strength on steel	3.7 N/mm
Stretch capability	300 %
temperature-resistant up to	150 °C
Type of adhesive tape	double-sided
Application	Sealing
Application	Attaching
Application	Assembly
Backing material	PE
Adhesive	Acrylate
Special features	moisture-resistant
Special features	clings well
Special features	resistant to high temperatures
Special features	damping
Special features	shear-resistant
"Best before" date	24 month