

**3M****VHB™ Power adhesive tape, Manufacturer's designation: 4910F****Order data**

Order number	083785 4910F
GTIN	4054596308503
Item class	08M

**Description****Version:**

**Double-sided** high-performance **adhesive tape** of pure acrylate adhesive (VHB) for permanently strong bonds. High instant tack, high resistance to temperature, weather, UV and solvents. Excellent sealing function, vibration-damping. Ideal for transparent joints and materials such as glass.

**Application:**

Suitable for metals, painted surfaces, painted wood, glass, ceramics and many plastics. For use indoors and outdoors.

Length: 11 m

Width: 19 mm

Colour: transparent

Short-term temperature-resistant to: 150 °C

Long-term temperature-resistant to: 90 °C

**Technical description**

Colour	transparent
Width	19 mm

Manufacturer's designation	9410F
Length	11 m
Thickness	1 mm
Material of covering	Siliconised PE film
Type of adhesive tape	double-sided
Adhesive	Acrylate
Special features	moisture-resistant
Special features	clings well
Special features	damping
Application	Sealing
Application	Attaching
Application	Assembly
"Best before" date	12 month
Stretch capability	300 %
Storage temperature	20 - 23 °C
Number of adhesive tapes	1
Backing material	PE
temperature-resistant up to	90 - 150 °C
Storage humidity	50 - 60 %
Adhesive strength on steel	2.6 N/mm