

**HOLEX**

## Face mill arbor with cooling channel bore, HSK-A 100 A = 100, Spigot Ø d1: 16mm



### Order data

Order number	306687 16
GTIN	4045197959782
Item class	32A

### Description

#### Version:

- Clamping Ø 40 with 4 tapped holes for drive blocks to DIN 2079.
- With Balluff/RFID chip bore.
- Increased collar contact surface.
- HSK mating faces machined.

With cooling channel bores.

#### Application:

For clamping shell end mills and milling cutter heads.

#### Supplied with:

Lock screw.

#### Optional extras:

Coolant tube No. 309880, socket wrench for coolant tubes No. 309890, toggle spanner No. 309840.

### Technical description

Suitable toggle spanner No. 309840	16
Spare milling cutter lock screw No. 309860 / 309861	16
External Ø D	38 mm
Overhang dimension A	100 mm

Milling mandrel length L <sub>4</sub>	17 mm
Clamping Ø D <sub>1</sub>	16 mm
Adapter	HSK-A 100 A = 100
Arbor standard	ISO 12164-1
Arbor standard	DIN 69882-3
Arbor standard	DIN 69893
Shape	A
Cooling channel bore	not pluggable
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 6 µm
Machining strategy	HPC
Type of product	Milling head arbor