


DOHT 070202 right-hand, W60, Type: K10

Order data

| | |
|--------------|---------------|
| Order number | 268855 K10 |
| GTIN | 4047109064577 |
| Item class | 24T |

Description

DOHT 070202 right-hand K10 Grade: K10

Cutting depth a_p : 0.5 - 2.5 mm

Feed f : 0.05 - 0.25 mm/rev.

Cutting speed v_c main application: 200 m/min

Cutting speed v_c secondary application: 300 - 500 m/min

Technical description

| | |
|---|---------------------|
| Cutting conditions | continuous |
| Cutting speed v_c main application | 200 m/min |
| Main application | K |
| Cutting speed v_c secondary application | 300 - 500 m/min |
| Feed f | 0.05 - 0.25 mm/rev. |
| Secondary application | N |
| Cutting depth a_p | 0.5 - 2.5 mm |
| Grade | K10 |

| | |
|---------------------------|------------------------------|
| ISO code indexable insert | DOHT 070202 R |
| Number of changes/inserts | 2 |
| Product name attribute | W60 |
| Rake | 12 degrees |
| Type of product | Indexable insert for turning |