



TOGX 06T104 neutral, W57, Type: CK3210

Order data

Order number	268864 CK3210
GTIN	4047109064089
Item class	24T

Description

TOGX 06T104 neutral CK3210 Grade: CK3210

Cutting depth a_p : 0.2 - 2.5 mm

Feed f : 0.05 - 0.2 mm/rev.

Cutting speed v_c main application: 120 - 300 m/min

Cutting speed v_c secondary application: 120 - 180 m/min

Technical description

Rake	14 degrees
Insert assignment	neutral
Indexable insert clearance angle	degrees
Product name attribute	W57
Indexable insert profile	
Type of product	