

**Bench grinding wheel D×T×H (mm), 150×20×32, Type: NK36****Order data**

Order number	596200 NK36
GTIN	9003171475746
Item class	53Y

Description**Version:**

High-quality long-lasting bench grinder wheels in ceramic bonding. Very low radial and axial run-out, maximum cutting speed 40 m/s. For **general use** on double-ended bench grinding machines for deburring, sharpening and resharpening tools.

Application:

For construction steels and low-alloy steels and also grey cast iron.

Specification:

Standard aluminium oxide grey-blue, hardness grade M.

Supplied with:

Reducing ring set for the indicated bores.

Note:

For compact deburring wheels see No. 568725 ff.

Technical description

Grinding media	Aluminium Oxide grit (A)
Grinding medium code	A

maximum circumferential speed	40 m/s
Grit designation	coarse
Grit	36
Specification	Standard aluminium oxide grey-blue, hardness grade M
Grinding process	Bench grinder
Reducing ring inner Ø	25 mm
Reducing ring inner Ø	20 mm
Reducing ring inner Ø	16 mm
Shape	1
Disc Ø D	150 mm
Disc thickness T	20 mm
Product name attribute	150×20×32
Bore Ø H	32 mm
Type of product	Grinding wheel for off-hand grinders