




Precision surface grinding wheel D×T×H (mm), 300×20×127, Type: C60



Order data

Order number	591805 C60
GTIN	9003170368902
Item class	53Y

Description

Version:

High performance surface grinding wheels with high-porosity bonding system for reduced thermal loading and minimal dressing diamond wear.

Open-pored **silicon carbide** grinding wheel with **low tendency to clog**. Suitable for grinding aluminium, NF metals, titanium, carbide and cast iron.

- **Universally applicable for reciprocating grinding processes, which significantly reduces the frequency of wheel changes in daily operation.**
- **For use on all commercially available grinding machines for tool and die making and machine tool building, e.g. Jung, ABA, Blohm, Elb, Mägerle, Ziersch & Baltrusch, Geibel & Hotz, Jones & Shipman.**
- **Cooling with emulsion is necessary, ensure good lubrication, especially on long-chipping materials.**

Application:

- **Universally applicable for reciprocating grinding processes, which significantly reduces the frequency of wheel changes in daily operation.**
- **Can be used on all commercially available grinding machines for tool and die making and machine tool building e.g. Jung, ABA, Blohm, Elb, Mägerle, Ziersch&Baltrusch, Geibel&Hotz, Jones&Shipman.**
- **Cooling with emulsion is necessary, ensure good lubrication, especially on long-chipping materials.**

Specification:
C60J11V18.**Note:**

Profile surface grinding wheels available on request.

Shape: 1

Shape: 1

Technical description

Grinding process	Surface grinding
Grinding media	Silicon carbide
Grinding medium code	SiC
Specification	C60J11V18
Shape	1
Product name attribute	300×20×127