



## Two-leg extractor with quick adjustment, Type: 10



### Order data

Order number	880400 10
GTIN	4021176644856
Item class	83U

### Description

#### Version:

With knurled grip for **quick loosening and moving** of the extractor legs **without additional tools**.

#### Application:

Universally capable of extracting bearings, gear wheels etc. **Can be used as external and internal extractor.**

### Technical description

Power	4.5 t
Internal capacity	70 - 180 mm
Depth of reach up to	100 mm
External clamping range	30 - 120 mm
maximum torque	80 Nm
External hexagon drive	17 mm

Number of hooks	2
Weight	1.44 kg
Type of product	Two-leg extractor