

● INNOVATEST®

Hardness testing machine Rockwell FENIX, Type: 200AR**Order data**

Order number	495071 200AR
GTIN	2050001957252
Item class	49G

Description**Version:**

Rockwell hardness testing machine with very high precision. Stiff machine frame, suitable even for rough workshop conditions. The test load is applied by a weigh application system. No power supply required.

Standard:

DIN EN-ISO 6508 and ASTM E-18

Supplied with:

HRC hardness comparison plate with grid. Ready-to-use basic equipment: Rockwell cone 120°, flat support table $\varnothing = 60$ mm. Including dispatch packaging.

Note:

Delivery charged separately. Please contact your specialist advisor with regard to calibrating the required load levels and methods. Further accessories such as Vee supports available on request.

Technical description

Pre-load test force	10 kg
Width	270 mm
Power supply	100 – 240 V / 50-60 Hz / 3A

Weight	122 kg
Scale divisions	1 HR
Main load test force	60, 100, 150 kg
Display	analogue dial gauge
maximum sample height	260 mm
Rockwell scales	A, B, C, D, E, F, G, H, K, L, M, P, R, S, V
Length	550 mm
Test procedure	Rockwell
maximum sample width	150 mm
Operation	manual
Height	765 mm
Power supply	Mains operated
Calibration	Price on request
Type of product	Hardness tester