

Garant**Table / bench vice with bench clamp, Jaw width: 80mm****Order data**

Order number	967030 80
GTIN	4045197612328
Item class	91J

Description**Version:****High clamping accuracy due to Vee form precision guide.**

Slides to the rear on opening. High-strength casting (GG 25) with a pearlitic structure. Long and particularly accurate **Vee form precision guide**. Precise spindle bearing, lead spindle is fully enclosed with trapezoidal thread and hence protected from dirt. Large face milled anvil area for light shaping work. The hardened steel jaws are ground and can be exchanged for serrated jaws (see spare jaws).

Application:

For clamping to the worktop.

Technical description

Opening direction	opens to the rear
Jaw capacity	100 mm
Weight	7 kg
Material	high-strength cast iron (GG 25)

Clamping range	0 - 60 mm
Jaw width	80 mm
Type of product	Machinist's vice

Accessories

Bench vice mounting plate, bamboo Size 300X250	967328 300X250
Pair of spare jaws serrated Jaw width 80 mm	967040 80
Pair of spare jaws smooth ground Jaw width 80 mm	967045 80
Bench vice mounting plate	967330