

**Garant**
**Arbor for screw-in milling cutters with thread, SK 40, Thread M×length L1:  
M10X181**

**Order data**

Order number	301313 M10X181
GTIN	4045197980687
Item class	31A

**Description**
**Version:**

**Vibration damped version, arbor with vibration-damping core.**

**Application:**

To take screw-in milling cutters with thread.

**Optional extras:**

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835.

Vibration: damped

Overhang dimension A: 200 mm

Bore  $\varnothing D_1$ : 10.5 mm

$\varnothing D_2$ : 18 mm

External  $\varnothing D$ : 35 mm

Reach  $L_1$ : 181 mm

$L_2$ : 7 mm

**Technical description**

Thread M	M10×181
$\varnothing D_2$	18 mm
Reach $L_1$	181 mm
Bore $\varnothing D_1$	10.5 mm
External $\varnothing D$	35 mm
$L_2$	7 mm

Overhang dimension A	200 mm
Adapter	SK 40
Arbor standard	ISO 7388-1
Shape	AD
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HSC
Vibration	damped
Type of product	Threaded copy mill arbor