

**Garant**
**Arbor for screw-in milling cutters with thread, SK 50, Thread M×length L1:  
M16X281**

**Order data**

Order number	301314 M16X281
GTIN	4045197981417
Item class	31A

**Description**
**Version:**

**Vibration damped version, arbor with vibration-damping core.**

**Application:**

To take screw-in milling cutters with thread.

**Optional extras:**

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835.

Vibration: damped

Overhang dimension A: 300 mm

Bore  $\varnothing D_1$ : 17 mm

$\varnothing D_2$ : 29 mm

External  $\varnothing D$ : 57 mm

Reach  $L_1$ : 281 mm

$L_2$ : 7.5 mm

**Technical description**

$\varnothing D_2$	29 mm
$L_2$	7.5 mm
Reach $L_1$	281 mm
External $\varnothing D$	57 mm
Bore $\varnothing D_1$	17 mm
Thread M	M16x281

Overhang dimension A	300 mm
Adapter	SK 50
Arbor standard	ISO 7388-1
Shape	AD
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HSC
Vibration	damped
Type of product	Threaded copy mill arbor