

Universal clamping device



Order data

Order number	967650
GTIN	2050001741554
Item class	97G

Description

Version:

Can be rotated or swivelled into the most favourable operating position by means of a ball joint. **Steel mandrel with external thread M18×1.5 and internal thread M10** for mounting jigs and fixtures. The ball joint can be locked immediately into any position with the high speed clamping lever. With screw-on base for screwing on to the worktop. Light metal alloy, hammer finish enamelled.

Suitable for:

Technician's vice No. 967590, 967600, 967610.

Technical description

Mounting spigot internal thread	M10
Pivoting range of ball joint	90 degrees
Weight	0.9 kg
Rotation range of ball joint	360 degrees
Mounting spigot external thread	M18×1.5
Type of product	Clamping fixture

