

**Garant**
**Jobber drill HSS-E N, uncoated, Ø DC h8: 4,3mm**

**Order data**

|              |               |
|--------------|---------------|
| Order number | 114400 4,3    |
| GTIN         | 4045197017581 |
| Item class   | 11B           |

**Description**
**Version:**

**Profile ground:** this ensures high concentricity and pitch accuracy. Precision ground point. Drill for production use.

**Reinforced core,** bright finish.

With point geometry shape C from size 2 mm

**Recommendation:**
**Maximum drilling depth:**

$$L_2 = L_c - 1.5 \times D_c.$$

**Technical description**

|  |              |
|--|--------------|
| Flute length $L_c$                       | 47 mm        |
| Feed $f$ in steel $< 750 \text{ N/mm}^2$ | 0.05 mm/rev. |
| Nominal $\varnothing D_c$                | 4.3 mm       |
| Number of cutting edges $Z$              | 2            |
| Tolerance nominal $\varnothing$          | h8           |
| Shank $\varnothing D_s$                  | 4.3 mm       |
| Overall length $L$                       | 80 mm        |
| Standard                                 | DIN 338      |
| recommended maximum drilling depth $L_2$ | 40.6 mm      |
| Point angle                              | 130 degrees  |
| Shank                                    | Plain shank  |

|                 |              |
|-----------------|--------------|
| Coating         | uncoated     |
| Tool material   | HSS E        |
| Type            | N            |
| Through-coolant | no           |
| Colour ring     | red          |
| Type of product | Jobber drill |

### User data

|                                | Suitability                               | V <sub>c</sub> | ISO code |
|--------------------------------|---|----------------|----------|
| Steel < 500 N/mm <sup>2</sup>  | suitable                                  | 40 m/min       | P        |
| Steel < 750 N/mm <sup>2</sup>  | suitable                                  | 30 m/min       | P        |
| Steel < 900 N/mm <sup>2</sup>  | suitable                                  | 25 m/min       | P        |
| Steel < 1100 N/mm <sup>2</sup> | suitable                                  | 10 m/min       | P        |
| Steel < 1400 N/mm <sup>2</sup> | suitable                                  | 8 m/min        | P        |
| TOOLOX 33                      | suitable                                  | 8 m/min        | H        |
| INOX < 900 N/mm <sup>2</sup>   | suitable                                  | 12 m/min       | M        |
| INOX > 900 N/mm <sup>2</sup>   | suitable only under restricted conditions | 8 m/min        | M        |
| Ti > 850 N/mm <sup>2</sup>     | suitable only under restricted conditions | 5 m/min        | S        |
| GG(G)                          | suitable                                  | 25 m/min       | K        |
| CuZn                           | suitable only under restricted conditions | 80 m/min       | N        |
| Uni                            | suitable                                  |                |          |
| Oil                            | suitable                                  |                |          |
| wet maximum                    | suitable                                  |                |          |