

**HOLEX****Roll of abrasive fleece, 100 mm × 10 m, Fleece structure: 280****Order data**

Order number	GG5110 280
GTIN	4045197575012
Item class	GGN

**Description****Version:**

**Synthetic nylon fleece impregnated with abrasive grit** in synthetic resin bonding. Contains no materials that could cause corrosion, for wet and dry use (**same as 556015; 556110; 556115**).

same as 556110.

**Advantage:**

- **Adapts to the component shape.**
- **The open structure prevents clogging and reduces heat development.**
- **Even and reproducible finish.**
- **Can be used wet or dry.**
- **Contains no materials that could cause corrosion.**

**Application:**

Can be used by hand, on hand block No. 556020 or on an orbital sander. **Medium / medium**

**fine:** Abrasive grit: aluminium oxide, can be used universally.

**Content:**

**4 rollers / bulk pack.**

**Note:**

**Only sold in bulk pack quantities, not supplied individually. Ordering information: 1 set = 1 bulk pack.**

## Technical description

Grit equivalent	280 - 360
Grit designation	medium fine
Colour	red
Version	A Very Fine
Fleece structure	280
Contents	4
Iron, sulphur and chlorine constituents	< 0.1 %
Roller width	100 mm
Roll length	10 m
Product name attribute	100 mm × 10 m
Type of product	Roll of abrasive fleece

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		

Stone	suitable only under restricted conditions
Paint	suitable
Uni	suitable
wet maximum	suitable only under restricted conditions
dry	suitable

---

## Accessories

Roll of abrasive fleece Fleece structure 280	556110 280
--	------------