



## Pneumatic impact wrench, Type: W2411



### Order data

Order number	079171 W2411
GTIN	7322590051266
Item class	03R

### Description

#### Version:

All technical data relate to a dynamic pressure of **6.3 bar** and the specified hose internal Ø.  
Powerful impact wrench.

Exhaust air passes through the handle, **reversible**.

· **Well balanced and ergonomic.**

#### Application:

Suitable for light assembly work.

#### Spare part:

**Selected service kits:** Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

### Technical description

Format	Pistol
Operating noise	88 dB(A)
Height	165 mm
Tool arbor size	3/8 in

Maximum screw $\varnothing$ (8.8 - 12.9)	M10
recommended hose size (internal $\varnothing$ )	10 mm
maximum air consumption	678 l/min
Torque range	13 - 80 Nm
maximum vibration to EN	7 m/s <sup>2</sup>
Manufacturer's designation	W2411
Weight	1 kg
maximum speed	7000 min <sup>-1</sup>
Length	154 mm
Tool arbor drive profile	□
Compressed air connection	1/4 in
Connection thread	BSP
Type of product	Screwdriver