



Clamping mandrel for through hole, D1: 7,4mm



Order data

Order number	370015 7,4
GTIN	4046368380008
Item class	37M

Description

Version:

- Base body of structural steel including steel screw.
- 5-face machining possible.
- Very high repetition accuracy.
- Easy machining of the base body at the desired clamping \emptyset .

Application:

For clamping workpieces in an existing bore.

Technical description

D ₂ smallest clamping \emptyset	4.1 mm
External \emptyset D ₁	7.4 mm
External \emptyset D	20 mm
max. clamping travel	0.13 mm
\emptyset D ₃	M 2
H ₁	7.6 mm

maximum tightening torque	0.7 Nm
Clamping force	1.1 kN
H	10.7 mm
Ø D ₄	M 2/13.7
Tolerance external Ø	h9
Type of product	Mandrel