



## Safety cabinet Q-Classic type 30, Width: 1200mm



### Order data

Order number	981035 1200
GTIN	4054923086739
Item class	96G

### Description

#### Version:

Cabinet body made of melamine resin-coated, fire-resistant special boards, door front of sheet steel.

- **Mountings for shelves at 32 mm intervals.**
- **Floor-level containment tray (satisfies StawaR).**
- **With exhaust air connection (NB 75).**
- **Lockable with profile half-cylinder, can be integrated into the company's locking system. Not compatible with the Hoffmann locking system.**

Base suitable for fork lift truck. 2-door

#### Application:

Storage of very small quantities of hazardous substances in working areas.

#### Standard:

DIN EN 14470-1, Typgeprüft (Brandkammergetestet), **30 Minuten feuerbeständig (nach Brandschutzstufe der TRGS 510 Anlage 3).**

#### Supplied with:

Cabinet with 3 storage shelves, perforated panel insert, and floor-level drip tray, plastic-coated, plus service log book.

#### Colour:

Cabinet casing anthracite grey RAL 7016, doors **signal blue RAL 5005.**

**Note:**

At regular intervals (annually), safety cabinets should be maintained and their operating characteristics checked by an authorised competent person.

**Technical description**

Width	1164 mm
Usable width	1050 mm
Depth	620 mm
Load capacity of shelf	75 kg
Volume of floor-level drip tray	33 l
Usable height	1626 mm
Weight	274 kg
Height	1947 mm
Number of perforated plate inserts	1
Usable depth	519 mm
Number of floor-level containment trays	1
Number of shelves	3
Height adjustment interval	32 mm
Colour selection	Body RAL 7016, fronts RAL 7035, 1004, 3020, 5010, 5005, 6011, 9010, 9006
Fire resistance	30 min
Type of product	Safety cabinet