



## NC8 NC high pressure vice, Type: 125M



### Order data

Order number	360405 125M
GTIN	4250364403368
Item class	34A

### Description

#### Version:

**Compact size:** Optimum ratio between clamping range and overall length. The clamping force can be pre-set **without using tools: in 11 steps:** Jaw width 90 mm, **in 4 steps:** Jaw width 125 / 160 / 200 mm. Particularly rigid base body of GJS-60, **top and bottom faces ground; pairing accuracy 0.02 mm.**

#### Feature:

**Fully enclosed low-maintenance nitrided spindle!**

- **Increased service reliability.**
- **Optimised swarf protection.**
- **Minimised cleaning requirement.**

**With 25H6 M10 holes at 200 mm pitch for zero-point clamping system.**

#### Application:

Can be used horizontally or laterally, **since the side faces are ground to an accuracy of -0.05 mm.**

#### Supplied with:

2 stepped jaws (= standard!), 1 crank handle, 4 table clamps.

#### Optional extras:

- **Clamping stud No. 360025 - 25 M10.**
- **Adapter plates for quick jaw change Xtric No. 361293;361294 size 125.**
- **Adapter plates No. 361297; 361298 size 125.**

#### Note:

- **Dimensions/jaws interface NC 8 identical to the Allmatic TC / LC.**
- **NC 8 (No. 360405) supersedes the products LC (No. 360500) and TC (No. 360400).**
- **Sizes 125 MX and 125 LX are supplied with jaws No. 361295 125 and No. 361296 125.**

## Technical description

Jaw height h	39.5 mm
t	144 mm
Colour code for suitable accessories	NC8
Base body length a	398 mm
Version	Zero-point clamping system
Overall length L	483 mm
Clamping range d	131 - 313 mm
Longitudinal slot I H7	20 mm
r ±0.015	118 mm
Clamping force up to maximum	40 kN
Base body height c -0.02	100 mm
Cross-slot n H7	20 mm
m	180 mm
Weight	35 kg
Type	125
Clamping range b	0 - 182 mm
Tenon width B <sub>1</sub> -0.05	126 mm
Number of threads for workpiece back-stop	4
Series	NC8
Type of product	Machine vice

## Accessories

Thread wiper set Type 125	360822 125
---------------------------	------------